



Steel-Rail Standard 28 mm Width

Rollers	Description	PBC Linear	ROLLON
–	Rail with Counterboare	SRS28R-XXXXC*	TLC-28-XXXX
–	Rail with Countersunk	SRS28R-XXXXV	TLV-28-XXXX
3	Short Carriage	SRS28C-3AS*	NSW28-3
4	Carriage - Configuration 4A	SRS28C-4AS	NSW28L-4A
4	Carriage - Configuration 4B	SRS28C-4BS	NSW28L-4B
4	Carriage - Configuration 4C	SRS28C-4CS	NSW28L-4C
5	Carriage - Configuration 5A	SRS28C-5AS	NSW28L-5A
5	Carriage - Configuration 5B	SRS28C-5BS	NSW28L-5B

* indicates an in-stock option. All other products have a 6 week lead time.

XXXX indicates rail length in mm (ex. 250mm = 0250)


MAX carriage loads are the same between PBC Linear and Rollon

Steel-Rail Standard 35 mm Width


Rollers	Description	PBC Linear	ROLLON
–	Rail with Counterboare	SRS35R-XXXXC*	TLC-35-XXXX
–	Rail with Countersunk	SRS35R-XXXXV	TLV-35-XXXX
3	Short Carriage	SRS35C-3AS*	NSW35-3
4	Carriage - Configuration 4A	SRS35C-4AS	–
4	Carriage - Configuration 4B	SRS35C-4BS	–
4	Carriage - Configuration 4C	SRS35C-4CS	–
5	Carriage - Configuration 5A	SRS35C-5AS	–
5	Carriage - Configuration 5B	SRS35C-5BS	–

Carriage mounting holes are NOT the same between PBC Linear and Rollon


3 Roller Short Carriage




Configuration 4A




Configuration 4B




Configuration 4C



Configuration 5A



Configuration 5B



Steel-Rail Standard 43 mm Width

Rollers	Description	PBC Linear	ROLLON
–	Rail with Counterboare	SRS43R-XXXXC*	TLC-43-XXXX
–	Rail with Countersunk	SRS43R-XXXXV	TLV-43-XXXX
3	Short Carriage	SRS43C-3AS*	NSW43-3
4	Carriage - Configuration 4A	SRS43C-4AS	NSW43L-4A
4	Carriage - Configuration 4B	SRS43C-4BS	NSW43L-4B
4	Carriage - Configuration 4C	SRS43C-4CS	NSW43L-4C
5	Carriage - Configuration 5A	SRS43C-5AS	NSW43L-5A
5	Carriage - Configuration 5B	SRS43C-5BS	NSW43L-5B



Steel-Rail Linear Guides SRP Rail Interchange Charts

Steel-Rail Plus 28 mm Width

Rollers	Description	PBC Linear	ROLLON
-	Rail with Counterboare	SRP28R-XXXXC*	TGC-28-XXXX
-	Rail with Countersunk	SRP28R-XXXXV	TGV-28-XXXX
3	Guiding Short Carriage	SRP28C-3AG*	RV28G-3
4	Guiding Carriage - Conf 4A	SRP28C-4AG	RV28G-4A
4	Guiding Carriage - Conf 4B	SRP28C-4BG	RV28G-4B
5	Guiding Carriage - Conf 5	SRP28C-5AG	RV28G-5
6	Guiding Carriage - Conf 6A	SRP28C-6AG	RV28G-6A
6	Guiding Carriage - Conf 6A	SRP28C-6BG	RV28G-6B
3	Rotating Short Carriage	SRP28C-3AR	RA28G-3
4	Rotating Carriage - Conf 4A	SRP28C-4AR	RA28G-4A
4	Rotating Carriage - Conf 4B	SRP28C-4BR	RA28G-4B
5	Rotating Carriage - Conf 5	SRP28C-5AR	RA28G-5
6	Rotating Carriage - Conf 6A	SRP28C-6AR	RA28G-6A
6	Rotating Carriage - Conf 6B	SRP28C-6BR	RA28G-6B
3	Floating Short Carriage	SRP28C-3AF*	RU28G-3
4	Floating Carriage - Conf 4A	SRP28C-4AF	RU28G-4A
4	Floating Carriage - Conf 4B	SRP28C-4BF	RU28G-4B
5	Floating Carriage - Conf 5	SRP28C-5AF	RU28G-5
6	Floating Carriage - Conf 6A	SRP28C-6AF	RU28G-6A
6	Floating Carriage - Conf 6B	SRP28C-6BF	RU28G-6B



Guiding Carriage



Rotating Carriage



Floating Carriage

Steel-Rail Plus 43 mm Width

Rollers	Description	PBC Linear	ROLLON
-	Rail with Counterboare	SRP43R-XXXXC*	TGC-43-XXXX
-	Rail with Countersunk	SRP43R-XXXXV	TGV-43-XXXX
3	Guiding Short Carriage	SRP43C-3AG*	RV43G-3
4	Guiding Carriage - Conf 4A	SRP43C-4AG	RV43G-4A
4	Guiding Carriage - Conf 4B	SRP43C-4BG	RV43G-4B
5	Guiding Carriage - Conf 5	SRP43C-5AG	RV43G-5
6	Guiding Carriage - Conf 6A	SRP43C-6AG	RV43G-6A
6	Guiding Carriage - Conf 6A	SRP43C-6BG	RV43G-6B
3	Rotating Short Carriage	SRP43C-3AR	RA43G-3
4	Rotating Carriage - Conf 4A	SRP43C-4AR	RA43G-4A
4	Rotating Carriage - Conf 4B	SRP43C-4BR	RA43G-4B
5	Rotating Carriage - Conf 5	SRP43C-5AR	RA43G-5
6	Rotating Carriage - Conf 6A	SRP43C-6AR	RA43G-6A
6	Rotating Carriage - Conf 6B	SRP43C-6BR	RA43G-6B
3	Floating Short Carriage	SRP43C-3AF*	RU43G-3
4	Floating Carriage - Conf 4A	SRP43C-4AF	RU43G-4A
4	Floating Carriage - Conf 4B	SRP43C-4BF	RU43G-4B
5	Floating Carriage - Conf 5	SRP43C-5AF	RU43G-5
6	Floating Carriage - Conf 6A	SRP43C-6AF	RU43G-6A
6	Floating Carriage - Conf 6B	SRP43C-6BF	RU43G-6B

3 Roller Configuration



Configuration 4A



Configuration 4B



Configuration 5



Configuration 6A



Configuration 6B



Visit pbclinear.com for Product Information
Call 1-800-962-8979 for Technical and Application Information